


UNDERCOUNTER KITCHEN SINK K-3356

Features

- 18-gauge stainless steel
- Undercounter
- Double (extra large/medium) compartment
- Includes installation hardware
- Rounded bowl(s)
- 9-1/2" (24.1 cm) deep left basin and 7-1/2" (19.1 cm) deep right basin (K-3356)
- 7-1/2" (19.1 cm) deep left basin and 9-1/2" (24.1 cm) deep right basin (K-3356-L)
- 32-7/8" (83.5 cm) x 17-7/8" (45.4 cm)



Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.3/CSA B45.4

Colors/Finishes

- NA: None applicable

Accessories:

- CP: Polished Chrome
- 0: White
- NA: None applicable
- Other: Refer to Price Book for additional colors/finishes

Specified Model

Model	Description	Colors/Finishes
K-3356	Undercounter sink with 9-1/2" (24.1 cm) deep left basin and 7-1/2" (19.1 cm) deep right basin	<input type="checkbox"/> NA
K-3356-L	Undercounter sink with 7-1/2" (19.1 cm) deep left basin and 9-1/2" (24.1 cm) deep right basin	<input type="checkbox"/> NA

Optional Accessories			
K-3191	Bottom basin rack (for extra large basin)	<input type="checkbox"/> 0 White	<input type="checkbox"/> Other _____
K-3278	Hardwood cutting board (for medium basin)	<input type="checkbox"/> NA	
K-3279	Wire basket (for extra large basin)	<input type="checkbox"/> 0 White	<input type="checkbox"/> Other _____
K-3291	Colander (for medium basin)	<input type="checkbox"/> 0 White	<input type="checkbox"/> Other _____
K-8801	Duostrainer® sink strainer	<input type="checkbox"/> CP	<input type="checkbox"/> Other _____

Product Specification:

The undercounter kitchen sink shall be 32-7/8" (83.5 cm) in length and 17-7/8" (45.4 cm) in width. Sink shall be made of 18 gauge stainless steel. Sink shall feature a double (extra large/medium) compartment with rounded bowls. Kohler Model K-3356 sink shall have a 9-1/2" (24.1 cm) deep left basin and a 7-1/2" (19.1 cm) deep right basin. Kohler Model K-3356-L sink shall have a 7-1/2" (19.1 cm) deep left basin and a 9-1/2" (24.1 cm) deep right basin. Sink shall include installation hardware. Sink shall be Kohler Model K-3356-_____.

UNDERTONE®

Technical Information




Dimensions shown for K-3356; sink dimensions are opposite for K-3356-L.		
Fixture*:	Basin area	Water depth
Sink, left	18" (45.7 cm) x 18" (45.7 cm)	9-1/2" (24.1 cm)
Sink, right	14" (35.6 cm) x 15" (38.1 cm)	7-1/2" (19.1 cm)
Drain holes	3-5/8" (9.2 cm) D.	
* Approximate measurements for comparison only.		

Included components:	
Hardware kit (4 required)	91915
Cut-out template (K-3356)	1040560-7
Cut-out template (K-3356-L)	1024848-7

Installation Notes

Install this product according to the installation guide.

Allow a minimum of 2" (5.1 cm) clearance around the sink rim for clip attachment.



Product Diagram